

## **PIPETTE TRADE IN & TRADE UP**



Save Up to 50% Off a New Gilson Pipette





## Promo Code: 6104

Upgrade to the standard in pipetting precision, accuracy, and comfort. Trade-in **ANY brand or model** of pipette (working or non-working) and save up to 50% OFF each new Gilson model. Choose from:

## **PIPETMAN®: RELIABILITY & ROBUSTNESS WITH EASY HANDLING**

- Legendary performance
- Low pipetting forces
- Built-to-last

## PIPETMAN® L: INCREASED COMFORT AND PRODUCTIVITY

- Lightweight and ergonomic
- Lockable volume settings
- All the benefits of the PIPETMAN, PLUS increased comfort and productivity

## PIPETMAN® M Connected: PIPETTE SMARTER. REPORT FASTER.

- Virtually no pipetting forces
- Save protocols directly to your pipette
- Pairs with TRACKMAN® Connected for increased reproducibility and traceability

Get an **additional 1-year protection** on top of our standard manufacturers' warranty with our new Extended Warranty cover. Ask your VWR Avantor Channel Rep for details, or ask them to add it to your order or quote for maximum protection and performance on your pipettes.







**Terms & Conditions:** \*Like for like trade-in applies. The same quantity of pipettes must be purchased as traded in. Discount off multichannels will only be valid when a multichannel is traded in. PIPETMAN and PIPETMAN and PIPETMAN L V-ring mulitchannels are available, please enquire for promo price. Promotion is available online and only valid in the US. Discount will apply to qualifying orders received by the Avantor VWR channel no later than 31 December 2025, or until promotional supplies are depleted. Trade-in pipettes and decontamination form must be postmarked within 30 days of order and no later than 1/31/26. Cannot be combined with any other promotions, discounts or special pricing agreements or on previously purchased products. Promotional pricing only available through the VWR Avantor channel and is not subject to liability ins. Discounts (offers) and the voltage of products or partners of Gilson or portunes of Gilson products or partners of Gilson or partners of Gilson products or partners of Gils via the "ORDER ENTRY" link on ywr.com. (Promotional part numbers cannot be found via Search on ywr.com.) For assistance with ordering, please contact Ayantor Customer Service at 1.800.932.5000, All prices in US dollars.



# **SEE ELIGIBLE SKUS BELOW!**

# Recycle ANY Brand Pipette with Gilson by Trading-in and SAVE!

| VWR Part<br>Number | Model        | Volume<br>(μL) | Trade-In<br>Price |
|--------------------|--------------|----------------|-------------------|
| PIPETMAN® Sing     | le Channel   |                |                   |
| MP76204-426        | P2           | 0.2 - 2        |                   |
| MP76204-428        | P10          | 1 - 10         | \$272             |
| MP76204-430        | P20          | 2 - 20         |                   |
| MP76204-432        | P100         | 10 - 100       |                   |
| MP76178-038        | P200         | 20 - 200       |                   |
| MP76204-436        | P1000        | 100 - 1000     |                   |
| MP76204-438        | P5000        | 500 - 5000     |                   |
| MP76204-440        | P10mL        | 1000 - 10000   |                   |
| PIPETMAN® Mul      | tichannel    |                |                   |
| MPF144068T         | P8 x 10      | 0.5-10         | \$566             |
| MPF144070T         | P8 x 20      | 2-20           |                   |
| MPF144072T         | P8 x 200     | 20 -200        |                   |
| MPF144074T         | P8 x 300     | 20-300         |                   |
| MPF144069T         | P12 x 10     | 0.5-10         | \$695             |
| MPF144071T         | P12 x 20     | 2-20           |                   |
| MPF144073T         | P12 x 200    | 20 -200        |                   |
| MPF144075T         | P12 x 300    | 20-300         |                   |
| PIPETMAN® L Si     | ngle Channel |                |                   |
| MP76204-442        | P2L          | 0.2 - 2        |                   |
| MP76204-444        | P10L         | 1 - 10         |                   |
| MP76204-446        | P20L         | 2 - 20         |                   |
| MP76204-448        | P100L        | 10 - 100       | \$298             |
| MP76204-450        | P200L        | 20 - 200       | <b>\$290</b>      |
| MP76204-452        | P1000L       | 100 - 1000     |                   |
| MP76204-454        | P5000L       | 500 - 5000     |                   |
| MP76204-456        | P10mLL       | 1000 - 10000   |                   |
| PIPETMAN® L M      | 1ultichannel |                |                   |
| MP76204-466        | P8 x 10L     | 0.5-10         |                   |
| MP76204-470        | P8 x 20L     | 2-20           | \$720             |
| MP76204-468        | P8 x 200L    | 20 -200        |                   |
| MP76204-472        | P8 x 300L    | 20-300         |                   |
| MPFA10039T         | P8 x 1200L   | 100-1200       |                   |
| MP76204-458        | P12 x 10 L   | 0.5-10         | \$904             |
| MP76204-462        | P12 x 20L    | 2-20           |                   |
| MP76204-460        | P12 x 200L   | 20 -200        |                   |
| MP76204-464        | P12 x 300L   | 20-300         |                   |
| MPFA10040T         | P12 x 1200L  | 100-1200       |                   |

| VWR Part<br>Number | Model           | Volume<br>(μL)   | Trade-In<br>Price |
|--------------------|-----------------|------------------|-------------------|
| PIPETMAN® M        | Connected Sin   | gle Channel      |                   |
| MPF81040T          | P10M            | 1 - 10           | \$604             |
| MPF81041T          | P20M            | 2 - 20           |                   |
| MPF81042T          | P100M           | 10 - 100         |                   |
| MPF81043T          | P200M           | 20 - 200         |                   |
| MPF81044T          | P300M           | 20-300           |                   |
| MPF81045T          | P1200M          | 100-1200         |                   |
| MPF81046T          | P5000M          | 500 - 5000       |                   |
| MPF81047T          | P10mLM          | 1000 - 10000     |                   |
| PIPETMAN® M        | Connected Mu    | Itichannel       |                   |
| MPF81048T          | P8X10M          | 1 - 10           |                   |
| MPF81050T          | P8X20M          | 2 - 20           |                   |
| MPF81052T          | P8X100M         | 10 - 100         | ¢1070             |
| MPF81054T          | P8X200M         | 20 - 200         | \$1079            |
| MPF81056T          | P8X300M         | 20-300           |                   |
| MPF81058T          | P8X1200M        | 100-1200         |                   |
| MPF81058T          | P12X10M         | 1 - 10           |                   |
| MPF81051T          | P12X20M         | 2 - 20           |                   |
| MPF81053T          | P12X100M        | 10 - 100         | \$1290            |
| MPF81055T          | P12X200M        | 20 - 200         |                   |
| MPF81057T          | P12X300M        | 20-300           |                   |
|                    | pricing and the | ne full range of |                   |





pipetman

## **NEED TIPS?**

Not all pipette tips are the created equally. PIPETMAN® DIAMOND Tips are made from the highest-grade material, manufactured in sterile, clean room environment, and are precision engineered to fit our pipettes perfectly for guaranteed performance. Ask your Gilson or VWR Avantor Account Manager for a complimentary tip sample with your trade-in pipettes!







## avantorsciences.com

Any prices, product, and/or services details are current when published and subject to change. Offers subject to product availability. Void where prohibited by law or company policy. Any claims concerning products manufactured by third parties are the sole claims of the manufacturer and not those of Avantor or its affiliates. All products are subject to the terms and conditions of sale of Avantor or its affiliates, including the applicable limitations of liability contained therein. The information herein should not be considered a warranty of any kind. Please carefully review any product information sheets and safety information for the product. Trademarks are owned by Avantor Inc. or its affiliates, unless otherwise noted. | Visit vwr.com and avantorsciences.com to view our privacy policy and additional disclaimers. © 2025 Avantor, Inc. All rights reserved.